



Korpus formy

Mold base

546x646




Wymiary i tolerancje
Dimensions and tolerances




	A	B	C	d	d2
PK	574	480	474	42	M16
PKA	558	440	458	54	M20

**PK 01
PKA 01**




	W
PK 01	646
PKA 01	596




PK 01 - 546 x 646 x h / material
PKA 01 - 546 x 646 x h / material

46	1730
56	2312
	2085

**PK 11
PKA 11**



	W
PK 11	646
PKA 11	596



PK 11 - 546 x 646 x h / material
PKA 11 - 546 x 646 x h / material

46	1730
56	2312
	2085



**PK 02
PKA 02**



**PK 12
PKA 12**




**PK 21
PKA 21**



PK 21 - 546 x 646 x h / material
PKA 21 - 546 x 646 x h / material

36	1730
46	2312
	2085



**PK 22
PKA 22**



PK 22 - 546 x 646 x h / material
PKA 22 - 546 x 646 x h / material

36	1730
46	2312
	2085

**PK 03
PKA 03**



PK 03 - 546 x 646 x h / material
PKA 03 - 546 x 646 x h / material

27	1730
36	2083
46	2085
56	2162
66	2311
76	2312
86	2738
96	Toolox33
116	Toolox44
136	2738HH
156	2714HH
176	
196	

Podcięcia do demontażu na życzenie.
Corner undercuts upon request.



Material info





Korpus formy

Mold base

546x646

PK 31



PK 31 – 546 x 646 x h / material

36	1730
46	2083
56	2085
66	2162
76	2311
86	2312
96	2343
116	2738
136	2767
156	Toolox33
176	Toolox44
196	2738HH
	2714HH



Podcięcia do demontażu na życzenie.
Corner undercuts upon request.



Material info




**PK 04
PKA 04**




PK 04 – 546 x 646 x h / material
PKA 04 – 546 x 646 x h / material

46	1730
56	2312
76	2085

**PK 05
PKA 05**




	A	B	M
PK 05	62	422	-
PKA 05	76	394	M12




PK 05 – 546 x 646 x h / material
PKA 05 – 546 x 646 x h / material

76	1730
86	2085
96	
116	
136	
156	
176	

**PK 55
PKA 55**




	A	B	M
PK 55	92	362	-
PKA 55	106	334	M12




PK 55 – 546 x 646 x h / material
PKA 55 – 546 x 646 x h / material

76	1730
86	2085
96	
116	
136	
156	
176	

**PK 06
PKA 06**



	A	B	C
PK 06	564	386	418
PKA 06	490	350	388




PK 06 – 546 x 646 x h / material
PKA 06 – 546 x 646 x h / material


27	1730
	2085

	d1
PK 06	M10
PKA 06	M12

**PK 65
PKA 65**



	A	B	C
PK 65	564	326	358
PKA 65	490	280	318




PK 65 – 546 x 646 x h / material
PKA 65 – 546 x 646 x h / material


27	1730
	2085

	d1
PK 65	M10
PKA 65	M12

**PK 07
PKA 07**



	A	B	C	D	M
PK 07	564	386	418	614	M4
PKA 07	490	350	388	608	M5




PK 07 – 546 x 646 x h / material
PKA 07 – 546 x 646 x h / material


36	1730
	2312
	2085

	d2
PK 07	M10
PKA 07	M12

**PK 75
PKA 75**



	A	B	C	D	M
PK 75	564	326	358	614	M4
PKA 75	490	280	318	608	M5



PK 75 – 546 x 646 x h / material
PKA 75 – 546 x 646 x h / material

36	1730
	2312
	2085

	d2
PK 75	M10
PKA 75	M12