



**Korpus formy**

Mold base

**696x696**



**Wymiary i tolerancje**  
Dimensions and tolerances




	A	B	C
<b>PK</b>	592	474	592
<b>PKA</b>	608	490	608


**PK 01  
PKA 01**



**PK 11  
PKA 11**



	W
<b>PK 11</b>	796
<b>PKA 11</b>	746




PK 11 - 696 x 696 x	h /	material
PKA 11 - 696 x 696 x	h /	
	46	1730
	76	2312
		2085


**PK 02  
PKA 02**




**PK 12  
PKA 12**



**PK 21  
PKA 21**





**PK 22  
PKA 22**



PK 22 - 696 x 696 x	h /	material
PKA 22 - 696 x 696 x	h /	
	46	1730
	56	2312
		2085

**PK 03  
PKA 03**



PK 03 - 696 x 696 x	h /	material
PKA 03 - 696 x 696 x	h /	
	27	1730
	36	2083
	46	2085
	56	2162
	66	2311
	76	2312
	86	2738
	96	Toolox33
	116	Toolox44
	136	2738HH
	156	2714HH
	176	
	196	

**Podcięcia do demontażu na życzenie.**  
Corner undercuts upon request.



**Material info**





**Korpus formy**

Mold base

**696x696**

**PK 31**



Podcięcia do demontażu na życzenie.  
Corner undercuts upon request.





**PK 31 – 696 x 696 x h / material**

h	material
46	1730
56	2083
66	2085
76	2162
86	2311
96	2312
116	2343
136	2738
156	2767
176	Toolox33
196	Toolox44
	2738HH
	2714HH

Material info




**PK 04  
PKA 04**




**PK 04 – 696 x 696 x h / material  
PKA 04 – 696 x 696 x h / material**

h	material
46	1730
56	2312
76	2085

**PK 05  
PKA 05**




	A	B	M
<b>PK 05</b>	84	528	-
<b>PKA 05</b>	76	544	M12




**PK 05 – 696 x 696 x h / material  
PKA 05 – 696 x 696 x h / material**

h	material
86	1730
96	2085
116	
136	
156	
176	

**PK 55  
PKA 55**




	A	B	M
<b>PK 55</b>	114	468	-
<b>PKA 55</b>	106	484	M12




**PK 55 – 696 x 696 x h / material  
PKA 55 – 696 x 696 x h / material**

h	material
86	1730
96	2085
116	
136	
156	
176	

**PK 06  
PKA 06**




	A	B	C
<b>PK 06</b>	610	488	524
<b>PKA 06</b>	540	500	538




**PK 06 – 696 x 696 x h / material  
PKA 06 – 696 x 696 x h / material**

h	material
27	1730
	2085

**PK 65  
PKA 65**




	A	B	C
<b>PK 65</b>	610	428	464
<b>PKA 65</b>	540	430	468




**PK 65 – 696 x 696 x h / material  
PKA 65 – 696 x 696 x h / material**

h	material
27	1730
	2085

**PK 07  
PKA 07**




	A	B	C	D	M
<b>PK 07</b>	610	488	524	-	-
<b>PKA 07</b>	540	500	538	658	M5




**PK 07 – 696 x 696 x h / material  
PKA 07 – 696 x 696 x h / material**

h	material
36	1730
	2312
	2085

**PK 75  
PKA 75**



	A	B	C	D	M
<b>PK 75</b>	610	428	464	-	-
<b>PKA 75</b>	540	430	468	658	M5



**PK 75 – 696 x 696 x h / material  
PKA 75 – 696 x 696 x h / material**

h	material
36	1730
	2312
	2085